


# HALFEN SANDWICHPLATTENANKER




## Übersicht verfügbarer Verbundanker

### Sandwichplattenanker SPA

Verfügbare Ankerhöhen H und Ankerlängen L [mm]														
Ankertyp	Rundstahl - Ø [mm] 05			Rundstahl - Ø [mm] 07			Rundstahl - Ø [mm] 09			Rundstahl - Ø [mm] 10				
	Best.-Nr.: SPA-1 0270. SPA-2 0271.	H	L	Best.-Nr.: SPA-1 0270. SPA-2 0271.	H	L	Best.-Nr.: SPA-1 0270. SPA-2 0271.	H	L	Best.-Nr.: SPA-1 0270. SPA-2 0271.	H	L	L	
	010-00001	160	265	010-00003	160	260								
	010-00002	180	305	010-00004	180	300								
				010-00005	200	340								
				010-00006	220	380	010-00138 <sup>①</sup>	220	375					
				010-00007	240	420	010-00139 <sup>①</sup>	240	415					
				010-00008	260	460	010-00111	260	455					
							010-00112	280	495					
							010-00113	300	535					
							010-00114	320	575					
							010-00115	340	615	010-00015	340	610		
							010-00116	360	655	010-00016	360	650		
										010-00103	380	690		
										010-00105	400	730		
										010-00107	420	770		

① gilt nur für SPA-1. Bestellnummern für SPA-2 siehe HALFEN-Preisliste.

### Verbundnadeln SPA-N, Verbundbügel SPA-B, Anstecknadeln SPA-A

Verfügbare Ankerhöhen H [mm]								
Ankertyp	Rundstahl - Ø [mm] 03		Rundstahl - Ø [mm] 04		Rundstahl - Ø [mm] 05		Rundstahl - Ø [mm] 06	
	Best.-Nr.: 0274.010-	H	Best.-Nr.: 0274.020-	H	Best.-Nr.: 0274.030-	H	Best.-Nr.: 0274.040-	H
	00001	120						
	00002	140						
	00003	160	00001	160				
	00004	180	00002	180				
	00005	200	00003	200				
			00004	220				
			00005	240	00001	240		
					00002	260		
					00003	280		
					00004	300		
					00005	320		
	Best.-Nr.: 0273.010-	H	Best.-Nr.: 0273.020-	H	Best.-Nr.: 0273.030-	H		
	00001	160	00001	160				
	00002	180	00002	180				
			00003	200				
			00004	220				
			00005	240	00001	240		
					00002	260		
					00003	280		
					00004	300		
					00005	320		
		Best.-Nr.: 0272.010-	H	Best.-Nr.: 0272.030-	H	Best.-Nr.: 0272.050-	H	
00001		120						
00002		140						
00003		160	00001	160				
00004		180						
			00002	200	00001	200		
			00003	250	00002	250		
					00003	280		
					00004	320		

Konstruktive Änderungen vorbehalten